

TECHKON

Erfolg ist messbar



TECHKON SpectroPlate



The model, a diva. The stylist loves details.
The photographer, a star.
And now it's up to you to bring it to paper.

Why measurements on printing plates?

Today in the age of Computer-to-Plate it is obvious: Without quality control in pre-press, there is no guarantee for quality in print.

Thus the measurement of the right dot transfer on offset printing plates is a key segment of comprehensive process control in the printing industry.

However, measurement is only useful if the appropriate measurement technology is applied.

Some years ago using densitometers on printing plates was common practice. But densitometers are designed for measuring on printed papers leading to limits when reading on plates.

At present, plate measurement devices based on microscopic image capture and processing are the established standard. TECHKON SpectroPlate unifies all advantages of this modern measurement technology in a compact, hand-held instrument.

TECHKON SpectroPlate – Digital MicroScope

How does SpectroPlate work ?

The measurement accuracy of a plate-measuring device is determined by the quality of the optical system and the performance of the image processing algorithms. SpectroPlate meets the highest standards in this respect.

The sample is illuminated uniformly with spectral broadband light. The microscopic image is captured by a precision optical lens system and a high resolution CMOS color matrix sensor with high dynamic range. The processing of the detailed color image is performed by a powerful graphic signal processor and sophisticated imaging algorithms. All relevant quality parameters for correctly manufactured printing plates are shown on the LC-display.

Versatile in use

Thanks to the excellent image capture quality and the ingenious graphic calculations, SpectroPlate can read precisely any screen size and screen technology: FM, AM or Hybrid screen. The spectrally white illumination and dynamic color evaluation permits reading all kinds of plate types and coated surfaces.

But it is not only plate reading where SpectroPlate shows its strengths. The multifunctional device handles dot measurement on film as well as on printed paper in CMYK print excellently.

Portable Microscope

SpectroPlate lets you see things normally hidden to the human eye. It shows the raster dots on a film or a printing plate in large magnification on the device display or optionally on a computer screen. It lets you visually judge printing plates and discover any soiling or exposure errors now that the structure of the raster dots is visible.

A specific strength is the image transfer of uncompressed high-resolution files to the PC where they can be stored, edited or sent over the internet. Geometric sizes of dots or lines can be retrieved in micrometer- or mils-dimensions.

Software SpectroConnect

The supplied Windows software connects the device to a PC. Measured values and transfer curves are displayed and stored. The display of comparisons to target values, the data export to Microsoft Excel™ and the compatibility to RIP-applications are additionally useful functions of SpectroConnect. An exceptional feature is the enlarged view of the microscopic images.



SpectroPlate

Versions and functions



SpectroPlate is available in three different types of performance packages: The entry-level model Start is designed for dot percentage measurements on all popular types of printing plates, film and CMYK print. The Expert version additionally features the recording of complete transfer curves and the possibility to analyze geometric objects within the device. The All-Vision model is able to measure supplementary low-contrast, processless printing plates.

SpectroPlate Start

- % dot percentage
- Screen angle in °
- Screen frequency in l/cm and lpi

SpectroPlate Expert

Same functions as SpectroPlate Start and additionally:

- Dot % transfer curve
- Dot gain transfer curve
- Geometric analysis
- Memory for 100 data sets
- Average measurement

SpectroPlate All-Vision

Same functions as SpectroPlate Expert and additionally:

- Measurement of chemistry-free, processless plates with very low visible contrast

The Start version can easily be upgraded to an Expert model by a post-purchase upload from the PC. All-Vision functionality is achieved by a hardware expansion.

All three types can easily be connected to the Windows software SpectroConnect which is included in the package.

All devices are factory-calibrated to a highly accurate reference printing plate resulting in high long-term absolute accuracy and an excellent inter-instrument agreement. Additionally, time-consuming calibration procedures prior to measurements are obsolete.

Software

SpectroConnect

System requirements: Windows XP, Vista, 7 or 8

Contents

- Measurement device SpectroPlate
- Charging console with white standard and AC adapter with universal plugs
- Carrying case
- USB cable
- CD with software SpectroConnect
- Manual with ISO 9000 compliant certificate

Specifications

Measurement technology	High-precision optical system with high resolution digital camera and digital image processing
Image capture	1024 x 1024 pixels, 16 million colors, RGB uncompressed
Measurement aperture	1 x 1 mm, direct positioning with viewfinder, real-time image preview captured in LC graphic device display
Light source	Homogeneous spectral-broadband LED illumination
Measurement time	Approximately 1 second per measurement
Calibration	Factory-made calibrated permanently, white standard in charging console
Measurement range dot %	0.0 – 100.0 %
Screen ruling range	AM: 30 – 150 l/cm, 75 – 380 lpi; FM: 10 – 70 microns
Measurable media	Offset printing plates – CtP and conventional, film in transmission and reflection, printed paper CMYK
Memory	100 data sets (only Expert and All-Vision)
Repeatability	± 0.5 %
Display	High-contrast, backlight LC graphic display, 240 x 160 pixels, 16 gray levels, contrast ratio adjustable
Power supply	Rechargeable NiMH battery, controlled recharge via charging console with AC adapter, 100 – 240 V, 47 – 63 Hz, up to 10.000 measurements per battery charge, battery level control
Communication Port	USB
Weight	530 grams
Dimensions	65 x 65 x 190 mm (approx. 2.6 x 2.6 x 7.5 inches)
System requirements for TECHKON software	Windows XP, Vista, 7 or 8; 32- and 64-bit, minimum: IBM-compatible PC with Intel Core Duo processor or comparable processor, 1 GB RAM, 2 USB ports